







HES2S-140-A125

Adjustable Concealed Hinge (Surface Mount)

- Surface mounts to the door frame for easy installation.
- Compact and sturdy design combined with an exceptionally simple install.
- Adjustable depth ±1/8" (3 mm), vertical ±1/8" (3 mm), horizontal with spacer ±1/16" (1 mm).
- Successfully passed 300,000 open/close private cycles.



ADJUSTABLE CONCEALED HINGE







HES2S-140-A125

- Surface mounts to the door frame for easy installation.
- Minimum door thickness is 1-1/2" (38 mm) or more.
- Opens to 125°. Door stopper is required to prevent breakage of the hinges and failure of the door.
- Successfully passed 300,000 open/close private cycles.
- Compact and sturdy design combined with an exceptionally simple install.
- Adjustable depth ±1/8" (3 mm), vertical ±1/8" (3 mm), horizontal with spacer ±1/16" (1 mm)



Application Image





No.






Back




With cover and plate removed






1	Body	POM	Dark Grey, Light Grey, Black		
2	Base Plate	SPCC	Nickel		
3	Arm	Zinc Alloy	Chemical Treatment		
4	Distance Plate	PBT			
(5)	Horizontal Adjustment Plate	POM	Dark Grey, Light Grey, Matte Black		
6	Socket Cover	ABS			
7	Base Plate Cover	ADO			



Y: Door Machining Margin	B: Door chamfering	A: Frame chamfering	
4 or below	1 or higher	1 or higher	
5	i oi nignei		


Cut Out Dimensions

Drill pilot holes at the positions of the adjustment and locating screws.



- ¹ When door machining margin is 3/16" (5 mm).
- ¹² The position of prepared hole for locating changes according to adjustment.

Door Position Adjustment



Adjust in the vertical/depth directions with oval hole screws and in the horizontal direction with the plate.

Item No.	Color	Door Width	Door Height	Door Thickness	Door Weight/ 2 pcs	Door Weight/ 3 pcs	Opening Angle
HES2S-140-A125-DGR	Dark Grey		Max. 106-5/16" (2700 mm)	Min. 1-1/2" (38 mm)	Max. 110 lbs (50 kg)	Max. 143 lbs (65 kg)	125°
HES2S-140-A125-LGR	Light Grey	Max. 35-7/16" (900 mm)					
HES2S-140-A125-BL	Matte Black	()					