

PRODUCT CATALOG








www.sugatsune.com


ONTENTS	Very Low Profile Range
duct Applications 2	VL-03: CLIP SET
hitectural Clip Selection Guide 2	VL-03H: HEAVY DUTY CLIP SET
ndard Profile Range	VL-03FR: FIRE RATED CLIP SET
PC-F1A: SELF TAPPING	Stratlock™ Range
PC-SF1: SURFACE MOUNT	Female Clips
PC-RF1-B: SIDE SURFACE MOUNT	O SL-SFA
PC-AF1: AUTO FIT	Male Clips
PC-DC1: MASONRY AND DRYWALL ADAPTER FOR PC-F1A	SL-M18
Male Clips	Metal Range
PC-M1B: SELF TAPPING	Female Clips
PC-M2H: SELF TAPPING HEAVY DUTY	MC-F5: SELF TAPPING MAXI METAL
PC-VM1: VARIO SELF TAPPING	MC-F10: SELF TAPPING MAXI METAL HEAVY DUTY
PC-VMX: VARIO SELF TAPPING HEAVY DUTY	Male Clips
PC-SM2: SURFACE MOUNT	MC-M5: MAXI METAL SELF TAPPING
PC-SM2H: SURFACE MOUNT	Textile Range
PC-SM1AC: SURFACE MOUNT ACOUSTIC PANEL LIGHTWEIGHT	Female Clips
PC-SVMX: SCREW FIX HEAVY DUTY	TC-F6H: TEXTILE CLIP QUICK RELEA
v Profile Range	Male Clips
Female Clips	TC-M6: TEXTILE CLIP SCREW-IN TY
LP-F8: SELF TAPPING	TC-SM6: TEXTILE CLIP SELF-
LP-DF8: SELF TAPPING COARSE THREAD	ADHESIVE TYPE
LP-AF8A: AUTO FIT	Panel Control
Male Clips	PS-150E: SELF TAPPING
LP-M8A: SELF TAPPING	PS-S150E: SURFACE MOUNT
LP-SM8AS:SURFACE MOUNT	Technical Notes
LP-SMX: SURFACE MOUNT	Installation Tools

Product Applications _____









Wall Panel Installation

Removal

Indirect Lighting Breakdown Furniture

Retail Seating Trim

Which Clips Should I Use?_____

Fastmount[®] clips vary in size, shape, and function for use in various applications. "Profile" refers to the thickness of the support substrate; the thickness and material of the support substrate will determine the type of clips best suited to your application:


Standard Profile Clips

- Self-tapping clips can be used in applications with support substrate 9/16" or thicker; surface mount clips can be used with thinner support materials such as steel frames.
- Self-tapping, surface mount, and side surface mount clip options available.
- For use with wall and ceiling panels.
- Clip option for curved panels available.
- PC-DC1 masonry adapter for PC-F1A available for brick, concrete, and drywall.




Low Profile Clips

For applications with support substrate 3/8" or thicker.
LP-DF8 Clip option for drywall mounting available (wall panels only).



Very Low Profile Clips

- Can be surface or recessed mounted no minimum substrate thickness.
- No specialized tools required for installation.
- VL clips can be used with a two part epoxy appropriate for the material of your substrate and panel.
- · Fire resistant model available.
- For light weight panels.



Metal Clips

- Metal clip to withstand high temperatures.
- Allows for tolerance and panel flex (self-centering).
- Provides acoustic and vibration isolation.



Textile Clips

- Enables quick installation and easy removal of cushions.
- Replaces hook-and-loop tapes, snaps, and straps for cushions on outdoor furniture and marine applications.



Architectural Clip Selection Guide

SUBSTRATE	PLYWOOD PANEL	MDF PANEL	PARTICLE BOARD	ACOUSTIC PANEL	HONEYCOMB PANEL
WOOD FRAMES	PC-F1A + PC-VM1 PC-F1A + PC-M2H PC-F1A + PC-SM2H	PC-F1A + PC-VM1 PC-F1A + PC-M2H	PC-F1A + PC-VM1 PC-F1A + PC-M2H	LP-F8 + LP-SM8AS	LP-F8 + LP-SM8AS
STEEL FRAMES	PC-SF1 + PC-M1B PC-SF1 + PC-M2H PC-SF1 + PC-SM2 PC-SF1 + PC-SM2H	PC-SF1 + PC-M1B PC-SF1 + PC-SM2H	PC-SF1 + PC-M1B PC-SF1 + PC-SM2H + glue thread	PC-SF1 + PC-SM2	PC-SF1 + PC-SM2
CONCRETE	PC-DC1 + PC-F1A + PC-VM1 PC-DC1 + PC-F1A + PC-M2H PC-DC1 + PC-F1A + PC-SM2H	PC-DC1 + PC-F1A + PC-VM1 PC-DC1 + PC-F1A + PC-M2H	PC-DC1 + PC-F1A + PC-VM1 PC-DC1 + PC-F1A + PC-M2H	PC-DC1 + PC-F1A + PC-SM1AC	PC-DC1 + PC-F1A + PC-SM2 PC-DC1 + PC-F1A + PC-SM2H
CONCRETE + WOOD FRAMES	PC-F1A + PC-M2H PC-F1A + PC-SM2 PC-F1A + PC-SM2H	PC-F1A + PC-M2H PC-F1A + PC-SM2 PC-F1A + PC-SM2H	PC-F1A + PC-M2H PC-F1A + PC-SM2 PC-F1A + PC-SM2H	Must use Wood Frames + LP-F8 + LP-SM8AS	Must use Wood Frames + LP-F8 + LP-SM8AS
DRYWALL	LP-DF8 + LP-M8A LP-DF8 + LP-SM8AS PC-DC1 + PC-F1A + PC-VM1 PC-DC1 + PC-F1A + PC-M2H PC-DC1 + PC-F1A + PC-SM2H	LP-DF8 + LP-M8A LP-DF8 + LP-SM8AS PC-DC1 + PC-F1A + PC-VM1 PC-DC1 + PC-F1A + PC-M2H	LP-DF8 + LP-M8A LP-DF8 + LP-SM8AS PC-DC1 + PC-F1A + PC-VM1 PC-DC1 + PC-F1A + PC-M2H	LP-DF8 + LP-SM8AS with HMA (hot glue) PC-DC1 + PC-F1A + PC-SM1AC	LP-DF8 + LP-SM8AS - with epoxy glue PC-DC1 + PC-F1A + PC-SM2 PC-DC1 + PC-F1A + PC-SM2H
PLYWOOD, MDF	PC-F1A + PC-M1B PC-F1A + PC-M2H PC-F1A + PC-SM2 PC-F1A + PC-SM2H	PC-F1A + PC-M1B PC-F1A + PC-M2H PC-F1A + PC-SM2 PC-F1A + PC-SM2H	PC-F1A + PC-M1B PC-F1A + PC-M2H PC-F1A + PC-SM2 PC-F1A + PC-SM2H	LP-F8 + LP-SM8AS	LP-F8 + LP-SM8AS - with epoxy glue

This Clip Selection Guide should be used as a general guide only. Please contact customer service for more detailed advice if required. For overhead panels, a trial installation is strongly recommended to prove compatibility of Fastmount® systems with the panels and substrates in your project.



Standard Profile Range ____

The Standard Profile Clips offer the greatest variety of installation options and can be used for both wall and ceiling panels. Self-tapping clips can be used in applications with support substrate 9/16" or thicker; surface mount clips can be used with thinner support materials such as steel frames.



Female Clips			
Item No.	Dimensions	Diagram	Description
PC-F1A	9/16* 14.8 mm 2 mm		SELF TAPPING Mounts into: 0.66" (16.8mm) hole drill with CT-01, CT-07 Install with: CT-03 Compatible with Standard Profile Male Clips: PC-M1B, PC-M2H, PC-VM1, PC-VMX, PC-SM1AC PC-SM2, PC-SM2H Box: 100 Carton: 500
PC-SF1	1-7/8" (48 mm) 1-7/16" (36 mm) 1-7/16" (36 mm) 1-7/16" (16.5 mm) 2×44 11/16" (16.5 mm) 9 ¹⁰ 3/16" (4.5 mm)		SURFACE MOUNT Affix with #6 screws. Compatible with Standard Profile Male Clips: PC-M1B, PC-M2H, PC-VM1, PC-VMX, PC-SM1AC PC-SM2, PC-SM2H Box: 100 Carton: 700
PC-RF1-B	(um 61) 1-1/2* (28 mm) (um 61) 1-1/2* (28 mm)		SIDE SURFACE MOUNTAffix with #6 screws.Compatible with Standard Profile Male Clips:PC-M1B, PC-M2H, PC-VM1, PC-VMX, PC-SM1ACPC-SM2, PC-SM2HBox: 100Carton: 1,000
PC-AF1	3x\phi4, \u00e96 1-11/16" (40 mm) 1-11/16" (40 mm) 1-15/16" (49.9 mm) 100 100 100 100 100 100 100 10	1.3/8" (035 mm) 1.3/8" (1 mm) (1 mm)	AUTO FIT Lateral adjustment for use with curved panels. Affix with #6 screws. Mounts into: 1-3/8" (35mm) hole Compatible with Standard Profile Male Clips: PC-M1B, PC-M2H, PC-VM1, PC-VMX, PC-SM1AC PC-SM2, PC-SM2H Box: 25 Carton: 100
PC-DC1	1-1/4* (3 mm) 1-3/16 (2 mm) (1/1/6* (2 mm) (1/1/6* (7 2 mm)	PC-DC1 self-tapped into 24mm hole in drywall PC-DC1 installed into 26mm hole in coorrete wall PC-FTA installed into PC-DC1 showing transverse adjustment	SELF TAPPINGMasonry Drywall Adapter for PC-F1AMounts into: 1" (24~26mm) holeUse with: PC-F1AInstall with: rubber mallet (not provided).Box: 100Carton: 600
Accessories		Installati	on Tools: Standard Profile



CP-01-ST STAINLESS STEEL TIP

Stainless Steel tip for marking panels made of hard materials. Fits into the PC-F1A, PC-SF1, PC-RF1 and PC-AF1 female clips. Use to mark hole center in panel for correct clip alignment.



CT-08 YARD KIT 6 TOOLS One each CT-01, CT-03, CT-05, CT-07, CT-09, and CT-10 in plastic box. Use to install self-tapping standard profile clips.



Standard Profile Range_



Male Clips

Item No.	Dimensions	Diagram	Description
PC-M1B	13/16" 13/16" 13/16" 11/16" 11/16" 11/16"		SELF TAPPINGMounts into: 3/8" (10mm) hole drilled with CT-01 or CT-09Fits into: PC-F1A, PC-SF1, PC-RF1, PC-AF1Install with: CT-10Pull Out Force: 11 lbs (5kg)Box: 100Carton: 2,000
РС-М2Н	201 302 305 516° (75 mm) (17 3 mm)	(9 mm) (9 mm) (1 mm) (1 mm)	SELF TAPPING HEAVY DUTYMounts into: 3/8" (10mm) drilled with CT-01 or CT-09Fits into: PC-F1A, PC-SF1, PC-RF1, PC-AF1Install with: CT-10Minimum panel thickness: 11/32" (9mm)Pull Out Force: 22 lbs (10kg)Box: 100Carton: 500
PC-VM1	2015 2015 2016 2016 11116'' 11116'' 2017 2018 2018 11116'' 11116'' 2018	1/8" (4 mm)	VARIO SELF TAPPING Variable gap, high shear strength. Mounts into: 3/8" (10mm) drilled with CT-01 or CT-09 Fits into: PC-F1A, PC-SF1, PC-RF1, PC-AF1 Install with: CT-10 Minimum panel thickness: 11/32" (9mm) Pull Out Force: 11lbs (5kg) Box: 100 Carton: 2,000
PC-VMX	BE 5/16° 11/16° 33 01 (7.5 mm) (17.3 mm	1/4" (7 mm)	VARIO SELF TAPPING HEAVY DUTYVariable gap, high shear strength.Mounts into: 3/8" (10mm) drilled with CT-01 or CT-09Fits into: PC-F1A, PC-SF1, PC-RF1, PC-AF1Install with: CT-10Minimum panel thickness: 11/32" (9mm)Pull Out Force: 33 lbs (15kg)Box: 100Carton: 500
PC-SM2	117.6 mm) •		SURFACE MOUNTAdhesive fix super-groove base.Fits into: PC-F1A, PC-SF1, PC-RF1, PC-AF1Pull Out Force: 11lbs (5kg)Box: 100Carton: 1,500
PC-SM2H	(18.7 mm)		SURFACE MOUNT HEAVY DUTYAdhesive fix super-groove base.Fits into: PC-F1A, PC-SF1, PC-RF1, PC-AF1Pull Out Force: 22 lbs (10kg)Box: 100Carton: 500
PC-SM1AC			SURFACE MOUNT ACOUSTIC FABRIC PANELLIGHTWEIGHTAdhesive fix directly onto panel.Fits into: PC-F1A, PC-SF1, PC-RF1, PC-AF1Pull Out Force: 4.4 lbs (2kg)Box: 100Carton: 1000
PC-SVMX			SURFACE MOUNT HEAVY DUTYScrew fix installation.Fits into: PC-F1A, PC-SF1, PC-RF1, PC-AF1Pull Out Force: 33 lbs (15 kg)Box: 100Carton: 500



Low Profile Range_

For applications with thin support substrates, 3/8" (10mm) or thicker. LP-DF8 option available for wall panel applications on drywall.

Female Clips			
Item No.	Dimensions	Diagram	Description
LP-F8	(9.5 mm)	(4 mm)	SELF TAPPING Mounts into: 1" (25-25.4mm) hole Fits into: Plywood and MDF boards. Install tool: CT-19, CT-20 Compatible with Low Profile Male Clips: LP-M8A, LP-SM8AS Box: 100 Carton: 500
LP-DF8	(13 mm)	1/2" (12 mm) 1/8" (4 mm) 1/8" (4 mm)	SELF TAPPING DRYWALL COARSE THREAD (Wall Panels Only)Mounts into: 15/16 ~ 1" (25-25.4mm) holeFits into: Drywall (sheetrock) and soft core materials 1/2" (12mm) or thicker.Install tool: CT-19, CT-20 in battery drill with correct clutch setting Compatible with Low Profile Male Clips: LP-M8A, LP-SM8AS Box: 100Box: 100Carton: 900
LP-AF8A	3x044, 06 19/16 m (um 6 72) 19/17 m (um 6 72) 19/17 m (um 6 72) 19/17 m (um 9 70) 19/17 m (um 9 70) 19/17 m (um 9 70)		AUTO FIT Lateral adjustment for use with curved panels. Affix with #6 countersunk screws. Mounts into: 1 3/8" (35mm) pre-drilled hole in substrate Fits into: Plywood, MDF, fiberglass, etc., 7/16" (10.5mm) or thicker. Compatible with Low Profile Male Clips: LP-M8A, LP-SM8AS Box: 25 Carton: 250
Male Clips			
Item No.	Dimensi	ions Diagram	Description

Item No.	Dimensions	Diagram	Description
LP-M8A	1/4" (6 mm)		SELF TAPPING (Wall Panels Only) Mounts into: Plywood & MDF type boards with ³ /8" (10mm) hole Fits into: LP-F8, LP-DF8, LP-AF8A Install with: CT-10 Pull Out Force: 11 lbs (5kg) Box: 100 Carton: 2,000
LP-SM8AS	1-3/16" (30 mm) 7/16" (11.3 mm) 20 20 20 20 20 20 20 20 20 20 20 20 20		SURFACE MOUNT (Wall Panels Only) Can be glued or screwed into place with a self-tapping 3/4" #4 screw. Mounts onto: Plywood or MDF panels. Fits into: LP-F8, LP-DF8, LP-AF8A Pull Out Force: 11 lbs (5kg) Box: 100 Carton: 500
LP-SMX	01-3/8" (35 mm) (12,53 mm) (12,53 mm) (12,53 mm) (12,53 mm) (11,55 mm) (11,55 mm)		SURFACE MOUNT (Wall and Ceilings Panels)Mounts into: Steel, aluminum and or fiberglass.Fits into: LP-F8, LP-AF8AInstall with: 3x#6 Countersink screwsPull Out Force: 33 lbs (15kg)Box: 100Carton: 500

Accessories



CP-08ST LOW PROFILE CLIP CENTER POINT - STEEL TIP

Stainless steel tip for marking panels made of hard materials. Fits into the LP-F8 and LP-DF8 female clips. Use to mark hole center in panel for correct clip alignment.

Installation Tools: Low Profile Series



LP-08Y YARD KIT LOW PROFILE

Contains tools for installing Low Profile Range clips and panel removal tool. Plastic box with CT-05, CT-09, CT-10, CT-19.



Very Low Profile Range

Perfect for mounting removable thin wall lightweight panels and facings. This clip set requires less depth compared to other Fastmount[®] ranges. No special installation tools are required; can be used with a two part epoxy appropriate for the material of your substrate and panel and/or screw fixed. Ideal for mounting panels where no drilling is preferred. Typical applications include wall panels, headboards and inspection panels. VL-03FR clips are made of flame retardant plastic, rated at UL94 V-0 for applications requiring fire rated materials.



VL-CP3 VERY LOW PROFILE CENTER POINT

Use to mark hole center in panel for correct clip alignment. Has stainless steel tip for marking panel or frame. Tip: Push fits into either side of nylon molding.

Installation: Female & Male Clips



GLUE

When fixed with adhesive (glue), use in accordance with manufacturer's instructions.

VL-SS3 STAINLESS STEEL SCREW

Custom type 303 stainless steel screw for fixing VL-M3 into panels down to 1/4" (5.5mm) thick.









Stratlock Range ____

The SL-SFA provides rapid installation of heavy panels to timber, steel or aluminium framework. Designed specifically for contract interior fit-out applications to reduce on-site installation time. Female installs onto side of framework with 2 x #8 panhead screws (20mm) in timber frames, and #8 tek screws (20mm) into steel or aluminium framework. Used with the SL-M18 male clip, the new solid internal load chassis creates 4mm supported movement of the panel in any direction at the first engagement before locking into place with an 39.7 lb (18kg) pull out load. The distance between the panel and substrate when installed is 10.5mm at the first click, and 5mm when pressed into final position. Patent Pending.



Installation Steps: Screw Fix Method



Accessories



CP-01-ST STAINLESS STEEL TIP


Stainless Steel tip for marking panels made of hard materials. Fits into the PC-F1A, PC-SF1, PC-RF1, PC-AF1, and SL-SFA female clips. Use to mark hole center in panel for correct clip alignment.



Metal Clip Range _

For applications with heavy panels or requiring heat resistance. These patent pending metal based clips are specifically designed to withstand high temperatures and to provide acoustic and vibration isolation. The self-centering design allows for tolerance and panel flexing as well as the ability to be heavy load bearing.

Female Clips			
Item No.	Diagram	Description	
MC-F5	Ø13/16" (20 mm)	SELF TAPPING MAXI METAL Affix with #6 screws. Install with: MC-IT5 Compatible with Maxi Metal Male Clip: MC-M5 Pull out force: 11 lbs (5kg)	
MC-F10		Box: 10 Carton: 100 SELF TAPPING MAXI METAL HEAVY DUTY Affix with #6 screws. Install with: MC-IT5 Compatible with Maxi Metal Male Clip: MC-M5 Pull out force: 22 lbs (10kg) Box: 10 Carton: 100	
Mala Clina			
Male Clips			
Item No.	Diagram	Description	
MC-M5		SELF TAPPING	



Accessories



MC-CP5 METAL CLIP CENTER POINT

Center point fits MC-F5 metal clip. Use to mark hole center in panel, for correct clip alignment. Has stainless steel tip for marking panel.





Installation Tools: Metal Clip Series

CT-09 PANEL DRILL 10MM FORSTNER TYPE

Use with Standard Profile, Low Profile and Maxi Metal Range. To drill blind holes in the back of panels.

MC-IT5 INSTALL TOOL FOR MC-F5 & MC-M5

For installation of self tapping male MC-M5 and female MC-F5 or MC-F10 into plywood or similar. Use battery drill with correct torque setting.

CT-05 PANEL REMOVAL TOOL

Stainless steel tool for removing covered (upholstered) panels. Do not use with painted panels.



Textile Clip Range _____

The Textile Range has been specifically designed for the mounting of soft textiles to hard surfaces. The hidden system locks into place, and can only be removed by unlocking the clip, providing added security under high winds and seas. Makes cushions simple to install, remove and replace. Typical applications include sun loungers, exterior and interior cushions, seat bases and backs.

Female Clips				
Item No.	Diagram	Description		
TC-F6H	Fabric Cushion	QUICK RELEASE TEXTILE FEMALE CLIP HEAVY DUTYAffix by sewing TC-F6H onto cushion with needle size 110/18 andV92 or T90 Bonded Outdoor Polyester Thread.Compatible with Male Textile Clip: TC-M6, TC-SM6Box: 100Carton: 500		

Male Clips		
Item No.	Diagram	Description
ТС-М6	Cushion TC-FBH sewn onto cushion F Gushion Typical section through (inicked, NTS) Typical section through (inicked, NTS) Typical section through (inicked, NTS)	TEXTILE MALE CLIP - SCREW-IN TYPE Affix with #6 screw. Compatible with Female Textile Clip: TC-F6H Break out load: 22 lbs (10kg)
TC-SM6	L Deck moulding	Box: 100 Carton: 500 TEXTILE MALE CLIP - SELF ADHESIVE TYPE
	Custion TC-F6H sewn orio custion Through Unicked, NTS) Deck moulding /seat base Custion Typical section through (locked, NTS) Custion Typical section through (locked, NTS) Custion Typical section through (locked, NTS) Custion Typical section through (locked, NTS)	Affix with adhesive backing - clips supplied with VHB tape backing. Compatible with Female Textile Clip: TC-F6H Break out load: 22 lbs (10kg) Box: 100 Carton: 500

Accessories



TC-CP6H

Textile Range centerpoint with stainless steel tip to mark hole center in panel for correct clip alignment. See install guide.











Panel Control _

Use in conjunction with standard or low-profile options like LP-SMX to provide additional security and control. Especially well suited for ceiling panels, exit corridors and heavy panels which must be accessed often.







Technical Notes

Pull-out force

The pull-out force will vary depending on the clip type and are specified on each product sheet. They are generally minimum 11 lb. (5kg) for typical standard range clips and 22 lb. (10kg) for heavy duty clips.

The shock load is less and can be as low as 4.4 lb (2kg), depending on the type of shock load. Clips never load simultaneously on a panel, so if a panel has 10 clips it does not mean the force required to remove the panel (or the force the panel will take) is 10x 11 lb. (5kg).

Clip spacing and panel loads

Panels need to be supported evenly around the perimeter to eliminate sagging. The clip spacing requirements will vary depending on the application. Although many of the Fastmount[®] clip sets will hold more than your theoretical panel load, the reality of unknown conditions means panels and clips could be subjected to shock loads (g-forces) from seismic shocks.

Fastmount® with different materials

You can mount Fastmount[®] clips into or onto most panel products such as plywood, MDF, plastic, fiberglass, HPL, sandwich panels and composite panels. It is not recommended to use very heavy materials. The LP-DF8 coarse thread female clip is designed to work with drywall, for wall panels only. Installation with the standard profile series should use 2-4 PC-VM1 or PC-VMX clips to relief shear tension and support panel weight.

Drill setting and self tapping clips

The clutch setting on battery drills when fitting clips varies from drill to drill. It will depend on the battery charge condition and on the material you are screwing into. Once 2 or 3 test clips have been fitted, you will have a good feel for a setting that screws the clips home, but does not over tighten them. If the clips are breaking, the drill setting is too powerful. Some hard materials require a chamfer at the hole edge.

Adhesives for surface mount clips

The patent pending super-groove design means the Fastmount[®] surface mount clips use a mechanical engagement to secure the clip, so adhesive selection is mostly dependent on the panel material. We recommend two-part epoxies that are suitable for panel materials. A typical two-part epoxy will hold the clip at over three times the clipping load 66-88 lb (30-40kg) per clip.


Layout for Wall Panels


(Standard or Low Profile)

Maximum recommended panel weight: 88 lbs (40kg). Maximum recommended panel size: 94-1/2" x 47-1/4" (2.4mx1.2m)

Layout for Large or Heavy Ceiling Panels (Standard Profile or Metal)

Maximum recommended panel weight: 66 lbs (30kg). Maximum recommended panel size: 94-1/2" x 47-1/4" (2.4mx1.2m)









Technical Notes Continued.

Layout for Large Wall Panels for SL-SFA (Stratlock[®] Range)

Maximum recommended panel weight: 110.2 lbs (50kg) per m2. Maximum recommended panel size: 94-1/2" x 47-1/4" (2.4mx1.2m)





Layout for Small or Lightweight Ceiling Panels

Notes



0

Installation Tools _____

For installation quality and performance, the following tools are available for use.

CT-01	3/8" (10MM) DRILL CARBIDE TIPPED For use with the Standard Profile and Low Profile ranges. For drilling through panel and creating pilot hole for CT-07.	CT-12	1-1/4" (31MM) HSS COUNTERSINK DRILL BIT WITH 3/8" (10MM) SHANK High speed steel (HSS) bit with 3/8" (10mm) shank used to countersink the edge of holes in hard materials. Designed for use with MDF, plywood, fiberglass, and plastics when preparing the material for self-tapping clips.
СТ-03	INSTALL TOOL FOR PC-F1A For use with Standard Profile clip PC-F1A. Use to install self tapping female PC-F1A with battery drill on correct torque setting.	CT-13A	11/16" (16.8MM) ONE STEP DRILL CARBIDE TIPPED For use with Standard Profile clip PC-F1A. Carbide tip drill with 16.8 diameter for drilling holes into fiberglass, carbon fiber and kevlar laminates.
CT-05	PANEL REMOVAL TOOL Stainless steel tool for removing upholstered panels. Not for use with painted panels.	CT-15	THREAD TAP FOR PC-F1A For use with Standard Profile clip PC-F1A. Tap tool for tapping thread to fit PC-F1A into fibreglass, aluminium or similar. Either drill hole with CT-13A or drill out 10mm hole with CT-07 then tap with CT-15.
CT-05H	PANEL REMOVAL TOOL WITH HOOK Dual purpose reinforced stainless steel tool with fold down hook for use with lacquered and/or textured panels.	CT-18DG	DRILL GUIDE INSTALLATION JIG FOR PC-RF1 Adjustable drill guide for use with the Standard Profile Clip, PC-RF1.
ст-07	STEP DRILL CARBIDE TIPPED For use with Standard Profile clip PC-F1A. Tungsten tip drill with 16.8mm diameter for drilling 10mm hole in frame.	СТ-19	INSTALL TOOL LOW PROFILE RANGE (ALUMINIUM) For use with Low Profile range. Aluminium install tool for female clips LP-F8 and LP-DF8 with battery drill on correct torque setting. Ideal for large quantity installations.
СТ-09	3/8" (10MM) FORSTNER TYPE DRILL CARBIDE TIPPED For use with Standard Profile, Low Profile and Metal ranges. For drilling blind holes into the back of panels.	CT-20	INSTALL TOOL LOW PROFILE RANGE (PLASTIC) For use with Low Profile range. Aluminium install tool for female clips LP-F8 and LP-DF8 with battery drill on correct torque setting. Ideal for large quantity installations.
CT-09DG	DRILL GAUGE FOR CT-09 DRILL BIT For use with CT-09 Forstner drill bit. Designed for depth control when blind drilling for Standard and Low Profile range male clips. Incorporates a sealed roller bearing for smooth operation, and is easily adjustable with an Allen wrench.	CT-22	TAP FOR MALE CLIPS IN STANDARD AND LOW PROFILE RANGES New product for tapping thread into hard materials for male clips, PC-M1B, PC-M2H, PC-VM1, PC-VMX, LP-M8A, MC-M5, PS-150, PS- 150E (self tapping male end).
СТ-10	INSTALL TOOL SELF TAPPING MALE CLIPS (ALUMINIUM) For use with Standard Profile, Low Profile and Panel Control range. Use to install self tapping male PC-M1B, PC-M2H, PC-VM1, PC-VMX, PS-150 and LP-M8 with battery drill on correct torque setting.	LP-08Y	YARD KIT LOW PROFILE Contains tools for installing Low Profile Range clips and panel removal tool. Plastic box with CT- 05, CT-09, CT-10, CT-19.





Inches

Measurement Conversions

LENGTH

cm	mm	inch	feet
1	10	0.394	0.0328
0.1	1	0.0394	0.00328
2.54	25.4	1	0.083
30.48	304.8	12	1

inch = mm \div 25.4 mm = inch x 25.4

WEIGHT

g	kg	oz	lb
1	0.001	0.0353	0.0022
1000	1	35.27	2.205
28.4	0.0284	1	0.0625
453.6	0.454	16	1

 $lb = kg \times 2.205$ $kg = lb \div 2.205$

FORCE

Ν	kgf	lbf
1	0.10197	0.225
9.807	1	2.205
4.448	0.454	1

 MOMENT

N • m	kgf • cm	lbs • in
1	10.197	8.85
0.0981	1	0.868
0.113	1.152	1

 $lbs \bullet in = kgf \bullet cm x 0.868$ kgf • cm = lbs • in ÷ 0.868 N • m = kgf • cm x 0.0981 kgf • cm = N • m ÷ 0.0981



TEMPERATURE

°C	°F
0	32
-17.77	0

 $^{\circ}C = (^{\circ}F - 32) \times 5 \div 9$ $^{\circ}F = ^{\circ}C \div 5 \times 9 + 32$

*All tools and figures are for reference only.

DISCLAIMER:

Specifications, features, illustrations, certifications and materials shown in this catalog are based upon the latest available information at the time of publication. Although descriptions are believed to be correct, accuracy cannot be guaranteed. Sugatsune reserves the right to make changes at any time, without notice or obligation, in finishes, materials, sizes, specifications and availability and disclaims any and all liability for typographical, printing or production errors or changes affecting the products and/or specifications contained herein.

Actual performance of products may vary based upon many factors and may be less than stated. Differences in construction and build materials, designs or configurations may affect product performance and therefore, the customer is solely responsible for making the final selection of the product(s) to be used and to assure that all performance, safety and warning requirements of the application are satisfied.



sugatsune.com



Sugatsune America 18101 Savarona Way, Carson, CA 90746 Toll Free: 800-562-5267 sales@sugatsune.com



Sugatsune Canada, Inc. 3775 Boulevard du Tricentenaire, Montréal, Québec H1B-5W3 Toll Free: 833-312-5267 support@sugatsune.ca www.sugatsune.ca

LIT-Fastmount-2023